



LED Display Product Data Sheet LTP-2657KM

Spec No.: DS30-2002-119

Effective Date: 05/13/2002

Revision: -

LITE-ON DCC

RELEASE

BNS-OD-FC001/A4

FEATURES

- * 2 inch (50.8 mm) MATRIX HEIGHT.
- * LOW POWER REQUIREMENT.
- * SINGLE PLANE, WIDE VIEWING ANGLE
- * SOLID STATE RELIABILITY.
- * 5x7 ARRAY WITH X-Y SELECT.
- * COMPATIBLE WITH USASCLL AND EBCDIC CODES.
- * STACKABLE HORIZONTALLY.
- * CATEGORIZED FOR LUMINOUS INTENSITY.


DESCRIPTION

The LTP-2657KM is a 2 inch (50.8 mm) matrix height 5x7 dot matrix display. This device is multicolor applicable display, which has gray face and white dot color. The AllnGaP Hyper Red LED chips are made from AllnGaP on a non-transparent GaAs substrate. The AllnGaP Green LED chips are made from AllnGaP on a non-transparent GaAs substrate.

DEVICE


PART NO.	DESCRIPTION
AllnGaP Hyper Red & AllnGaP Green	Anode Column
LTP-2657KM	Cathode Row

PACKAGE DIMENSIONS



NOTES: All dimensions are in millimeters. Tolerances are ± 0.25 mm (0.01") unless otherwise noted.

INTERNAL CIRCUIT DIAGRAM



PIN CONNECTION

NO.	CONNECTION	NO.	CONNECTION
1	ANODE COLUMN 1 (GREEN)	15	ANODE COLUMN 5 (GREEN)
2	ANODE COLUMN 1 (RED ORANGE)	16	ANODE COLUMN 5 (RED ORANGE)
3	CATHODE ROW 7 (GREEN)	17	CATHODE ROW 1 (GREEN)
4	CATHODE ROW 7 (RED ORANGE)	18	CATHODE ROW 1 (RED ORANGE)
5	ANODE COLUMN 2 (GREEN)	19	ANODE COLUMN 4 (GREEN)
6	ANODE COLUMN 2 (RED ORANGE)	20	ANODE COLUMN 4 (RED ORANGE)
7	ANODE COLUMN 3 (GREEN)	21	ANODE COLUMN 3 (GREEN)
8	ANODE COLUMN 3 (RED ORANGE)	22	ANODE COLUMN 3 (RED ORANGE)
9	CATHODE ROW 5 (GREEN)	23	CATHODE ROW 3 (GREEN)
10	CATHODE ROW 5 (RED ORANGE)	24	CATHODE ROW 3 (RED ORANGE)
11	CATHODE ROW 4 (GREEN)	25	CATHODE ROW 4 (GREEN)
12	CATHODE ROW 4 (RED ORANGE)	26	CATHODE ROW 4 (RED ORANGE)
13	CATHODE ROW 6 (GREEN)	27	CATHODE ROW 2 (GREEN)
14	CATHODE ROW 6 (RED ORANGE)	28	CATHODE ROW 2 (RED ORANGE)

ABSOLUTE MAXIMUM RATING AT T_A=25°C

PARAMETER	AllInGaP GREEN	AllInGaP Hyper RED	UNIT
Average Power Dissipation Per Dot	35	40	mW
Peak Forward Current Per Dot	60	90	mA
Average Forward Current Per Dot	13	15	mA
Derating Linear From 25°C Per Dot	0.17	0.2	mA/°C
Reverse Voltage Per Dot	5		V
Operating Temperature Range	-35°C to +85°C		
Storage Temperature Range	-35°C to +85°C		
Solder Temperature 1/16 inch Below Seating Plane for 3 Seconds at 260°C			

ELECTRICAL / OPTICAL CHARACTERISTICS AT T_A=25°C

AllInGaP GREEN

PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT	TEST CONDITION
Average Luminous Intensity	I _v	1300	3600		μcd	I _p =32mA 1/16DUTY
Peak Emission Wavelength	λ _p		571		nm	I _F =20mA
Spectral Line Half-Width	Δλ		15		nm	I _F =20mA
Dominant Wavelength	λ _d		572		nm	I _F =20mA
Forward Voltage any Dot	V _F		2.05	2.6	V	I _F =20mA
			2.3	2.8	V	I _F =80mA
Reverse Current any Dot	I _R			100	μA	V _R =5V
Luminous Intensity Matching Ratio	I _v -m			2:1		I _p =32mA 1/16DUTY

AllInGaP Hyper RED

PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT	TEST CONDITION
Average Luminous Intensity	I _v	1650	2700		μcd	I _p =32mA 1/16DUTY
Peak Emission Wavelength	λ _p		650		nm	I _F =20mA
Spectral Line Half-Width	Δλ		20		nm	I _F =20mA
Dominant Wavelength	λ _d		639		nm	I _F =20mA
Forward Voltage any Dot	V _F		2.1	2.6	V	I _F =20mA
			2.3	2.8	V	I _F =80mA
Reverse Current any Dot	I _R			100	μA	V _R =5V
Luminous Intensity Matching Ratio	I _v -m			2:1		I _p =32mA 1/16DUTY

Note: Luminous intensity is measured with a light sensor and filter combination that approximates the CIE (Commission Internationale De L'Eclairage) eye-response curve.

TYPICAL ELECTRICAL / OPTICAL CHARACTERISTIC CURVES

(25°C Ambient Temperature Unless Otherwise Noted)




Fig1. RELATIVE INTENSITY VS. WAVELENGTH




Fig2. RELATIVE LUMINOUS EFFICIENCY (LUMINOUS INTENSITY PER UNIT CURRENT) VS. PEAK CURRENT (REFRESH RATE 1KHz)




Fig3. FORWARD CURRENT VS. FORWARD VOLTAGE




Fig4. RELATIVE LUMINOUS INTENSITY VS. FORWARD CURRENT




Fig5. MAX AVERAGE FORWARD CURRENT VS. AMBIENT TEMPERATURE.




Fig6. MAX. PEAK CURRENT VS. DUTY CYCLE % (REFRESH RATE 1KHz)

NOTE : KD=AlInGaP HYPER RED
KG=AlInGaP GREEN