


**BOTTOM VIEW POLARITY**



ELECTRO-OPTICAL CHARACTERISTICS $T_A=25^\circ\text{C}$ $I_f=20\text{mA}$					
PARAMETER	MIN	TYP	MAX	UNITS	TEST COND
PEAK WAVELENGTH		636 (RED)		nm	
		574 (GREEN)		nm	
		470 (BLUE)		nm	
FORWARD VOLTAGE (R)		1.9	2.5	$V_f$	
(G)		2.1	2.5	$V_f$	
(B)		3.65	4.2	$V_f$	
REVERSE VOLTAGE	5.0			$V_r$	$I_r=100\mu\text{A}$
AXIAL INTENSITY (R/G/B)		600/450/150		mcd	$I_f=20\text{mA}$
VIEWING ANGLE		30		2x theta	
EMITTED COLOR:	RED/GREEN/BLUE (MULTI-COLOR)				
EPOXY LENS FINISH:	WATER CLEAR				

**LIMITS OF SAFE OPERATION AT 25°C PER CHIP**

PARAMETER	COLORS	MAX	UNITS
PEAK FORWARD CURRENT*	(R/G/B)	185/205/160	mA
STEADY CURRENT		30	mA
POWER DISSIPATION (R/G/B)		170/105/102	mW
DERATE FROM 25°C		-1.2	mW/°C
OPERATING, STORAGE TEMP.		-40 TO +85	°C
SOLDERING TEMP.		+260	°C
2.0mm FROM BODY			3 SEC. MAX

\*  $t < 10\mu\text{s}$

\*UNLESS OTHERWISE SPECIFIED TOLERANCES PER DECIMAL PRECISION ARE: X=±1 (±0.039), X.X=±0.5 (±0.020), X.XX=±0.25 (±0.010), X.XXX=±0.127 (±0.005). LEAD SIZE=±0.05 (±0.002), LEAD LENGTH=±0.75 (±0.030), MIN. <sup>+DECIMAL PRECISION</sup> <sub>-0.00</sub> MAX. = <sup>+0.00</sup> <sub>-DECIMAL PRECISION</sub>

REV.	PART NUMBER <b>SSL-LX5099SIUBSUGB</b>	<p><small>CONFIDENTIAL INFORMATION</small></p> <p>THE INFORMATION CONTAINED IN THIS DOCUMENT IS THE PROPERTY OF LUMEX INC. EXCEPT AS SPECIFICALLY AUTHORIZED IN WRITING BY LUMEX INC, THE HOLDER OF THIS DOCUMENT SHALL KEEP ALL INFORMATION CONTAINED HEREIN CONFIDENTIAL AND SHALL PROTECT SAME IN WHOLE OR IN PART FROM DISCLOSURE AND DISSEMINATION TO ALL THIRD PARTIES.</p> <p><small>RELIABILITY NOTE</small></p> <p>OUR MANY YEARS OF EXPERIENCE DATA ACCUMULATION INDICATE THAT SOLDER HEAT IS A MAJOR CAUSE OF EARLY AND FUTURE FAILURE. PLEASE PAY ATTENTION TO YOUR SOLDERING PROCESS.</p>	<p>290 E. HELEN ROAD PALATINE, IL 60067-6976 PHONE: +1.847.359.2790 US WEB: www.lumex.com TW WEB: www.lumex.com.tw</p>											
T-5mm (T-1 3/4) LED, 6 LEADED, MULTI-COLORED, 636nm AlInGaP RED/574nm AlInGaP GREEN BICOLOR, 470nm ULTRA SUPER BLUE, WATER CLEAR LENS.		<table border="1" style="width:100%; border-collapse: collapse;"> <tr> <td style="width: 25%;">DRAWN BY:  KS/CT</td> <td style="width: 25%;">CHECKED BY:</td> <td style="width: 25%;">APPROVED BY:</td> <td style="width: 25%;">DATE: 4.6.02</td> </tr> <tr> <td></td> <td></td> <td></td> <td>PAGE: 1 OF 1</td> </tr> <tr> <td></td> <td></td> <td></td> <td>SCALE: N/A</td> </tr> </table>	DRAWN BY:  KS/CT	CHECKED BY:	APPROVED BY:	DATE: 4.6.02				PAGE: 1 OF 1				SCALE: N/A
DRAWN BY:  KS/CT	CHECKED BY:	APPROVED BY:	DATE: 4.6.02											
			PAGE: 1 OF 1											
			SCALE: N/A											